

thePassa P360 DALI-2 S UP WH

Item no.: 2010390



Presence and motion detectors Indoor detectors

Description

- Passive infra-red presence sensor for flush-mounted ceiling installation, DALI-2 certified
- Rectangular detection area 360°, 30 x 4,5 m, (135 m²) at mounting height 3 m, for corridors and storage areas, with 2 individually connectable and disconnectable detection zones
- This device provides information about presence and brightness in the form of a DALI telegram in line with IEC 62386 Part 303/304
- 3 instances for presence – detection area zone 1 + 2 / zone 1 / zone 2
- 2 mixed light measurements
- 3 instances for brightness – detection area zone 1 + 2 / zone 1 / zone 2
- Easy to calibrate brightness measurement
- Test mode for checking function and detection area
- Configurable detection sensitivity
- Can be configured via DALI bus or remote control
- The „theSenda S“ or „theSenda B“ user remote controls can be used to dim or switch the lamps, to control the blinds, or to execute additional functions via the higher-level control
- Ceiling installation in flush-mounted box
- Surface-mounted installation possible with surface frame 110A (optional)
- Area restriction with cover clips (optional)
- „theSenda B“ app remote control (optional) and corresponding „theSenda Plug“ app (for iOS/Android)
- A Multi-Master Application Controller is required for commissioning/control and configuration. According to IEC 62386, this must include parts 101/103 and optionally 301/303/304



Technical data

thePassa P360 DALI-2 S UP WH	
Operating voltage	DALI
Installation height	2 – 6 m
Maximum height	15 m
Minimum height	> 1,7 m
Installation type	Ceiling installation
Colour	White

thePassa P360 DALI-2 S UP WH	
Switching output	Sensor DALI
Stand-by consumption	≤10 mA
Light measurement	Mixed light measurement
Setting range brightness	10 – 10000 lx
Stand-by brightness	1 – 25 %
Max. cable cross section	max. 2 x 2,5 mm²

Subject to technical changes and misprints

additional information at: www.theben.de/product/2010390

The load data are determined with exemplary selected illuminants and are therefore typical data due to the large number of available products.

23/10/2021

Page 1 of 3

thePassa P360 DALI-2 S UP WH

Item no.: 2010390


theben
energy saving comfort

Technical data

thePassa P360 DALI-2 S UP WH		thePassa P360 DALI-2 S UP WH	
Size of concealed housing	Ø 55 mm (NIS, PMI)	Ambient temperature	-15°C ... 50°C
Detection range	150 m² (30,0 x 5 m)	Type of protection	IP 54 (when fitted)

Detection range for planning applications

Mounting height (A)	Diagonally (t)	Head on to (R)
2 m	56 m² 16 m x 3.5 m	56 m² 16 m x 3.5 m
2.5 m	88 m² 22 m x 4 m	72 m² 18 m x 4 m
3 m	135 m² 30 m x 4.5 m	90 m² 20 m x 4.5 m
3.5 m	150 m² 30 m x 5 m	100 m² 20 m x 5 m
4 m	150 m² 30 m x 5 m	100 m² 20 m x 5 m
4.5 m	150 m² 30 m x 5 m	100 m² 20 m x 5 m
5 m	150 m² 30 m x 5 m	100 m² 20 m x 5 m
5.5 m	150 m² 30 m x 5 m	100 m² 20 m x 5 m
6 m	150 m² 30 m x 5 m	100 m² 20 m x 5 m



Detection range according to Sensnorm IEC 63180

Mounting height (A)	Diagonally (T)	Head on to (R)
2.5 m	215 m² 43 m x 5 m	62 m² 14.8 m x 4.2 m
6 m	550 m² 50 m x 11 m	495 m² 45 m x 11 m
15 m	800 m² 40 m x 20 m	600 m² 30 m x 20 m

Subject to technical changes and misprints

additional information at: www.theben.de/product/2010390

The load data are determined with exemplary selected illuminants and are therefore typical data due to the large number of available products.

23/10/2021


Page 2 of 3

thePassa P360 DALI-2 S UP WH

Item no.: 2010390

theben
energy saving comfort

Scale drawings



Accessories

theSenda P

Item no.: 9070910




theSenda S

Item no.: 9070911




Surface frame 110A WH

Item no.: 9070912




Masking clip

Item no.: 9070921



QuickSafe

Item no.: 9070531



theSenda B

Item no.: 9070985



Cover 110 GR

Item no.: 9070591



Ceiling installation box 68A

Item no.: 9070992



Subject to technical changes and misprints

additional information at: www.theben.de/product/2010390

The load data are determined with exemplary selected illuminants and are therefore typical data due to the large number of available products.

23/10/2021

Page 3 of 3